



SYRINGE PUMP



407-412, 4th Floor, Span Centre,
South Avenue, Santacruz (W),
Mumbai - 400 054, India.

+91 22 2605 6666

+91 22 2605 6060

biox@biox.co.in

www.bio-xmedical.com
www.biox.co.in




SYRINGE PUMP

We would like to introduce ourselves as the suppliers of Syringe Pumps.

The Syringe Pumps have the following features :

- ➡ Module Design For Easier Local Service.
- ➡ Double CPU To Ensure Higher Reliability.
- ➡ General Graphic Identification.
- ➡ Manufacturing According To European ISO13485.
- ➡ Rohs & CE Qualified.



SPECIFICATIONS:

Model No. / Parameters		BXSP I I	BXSP I 2
Channel		Single	Double
Syringe Size		20, 50ml	5, 10, 20, 30, 50/60ml
Infusion Modes		Rate Mode, Rate-Time, Rate-VTBI, Time-VTBI, Body weight	
Safety		Double CPU to make sure higher standard infusion	
Drug Library		20 drug list with drug code display	
Accuracy		±2%	
Time Preset		00:01-99: 59 (Hour: Min)	
Volume Range		0-9999.9ml	
Flow Rate Step by		0.1 ml/h when rate < 100ml/h, 1ml/h when rate ≥ 100ml/h	
		5ml Syringe 0.1ml/h-150ml/h	
		10ml Syringe 0.1ml/h-300ml/h	
		20ml Syringe 0.1ml/h-600ml/h	
		30ml Syringe 0.1ml/h-900ml/h	
		50/60ml Syringe 0.1ml/h-1200ml/h	
Purge / Bolus		5ml Syringe 150ml/h; 10ml Syringe 300ml/h; 20ml Syringe 600ml/h	
Rate / Top Flow Rate		30ml Syringe 900ml/h; 50/60ml Syringe 1200ml/h	
Audible & Visible Alarms		Auto Seft-Test, Syringe Dislocation, Occlusion, Near End, Syringe Empty, VTBI Completion, Low Battery Exhausted, motor Malfunction, Incorrect Syringe Specification, Circuit Malfunction, Master CPU Malfunction, Monitoring CPU malfunction, Parameters Over Limitation, A.C Disconnection, A.C connection	
KVO		0.1-5.0ml/h Adjustable	
Occlusion Pressure	High:	40 KPa±20KPa	
	Middle:	60 KPa±20KPa	
	Low:	100 KPa±20KPa	
Max Infusion Pressure		120KPa	
Battery		≥8 hours	≥4 hours
Power Consumption		30VA	45VA
Power Supply		AC: 100-240V, 50Hz/60Hz	
Battery		Lithium battery, 11.1/2000mAh	
Classification		Class I, type CF, IPX4	
Dimension		26x21.5x11cm	32x21.5x20cm
Weight		2kg	3kg
Optional Function		Ambulance DC: 12V	