

Brinell Image Analysis System (B.I.A.S.)

The B.I.A.S. virtually eliminates operator influence:

It is found that measuring Brinell indentations can result in measurement errors between operators. This B.I.A.S. can virtually eliminate operator influence on test results.

Just place and click! Operating B.I.A.S. is easy:

With this handy instrument entire test sequence is simple. Place the scan hand on the work piece and move it so the impression appears near the middle of the screen. Just touch on 'Auto' in tool bar on laptop. The B.I.A.S. automatically measures the diameter of indentation with resolution of 0.01mm and displays Brinell value with diameter measurement. All data storage functions are automatically performed according to batch parameters.

The B.I.A.S. can be configured to meet your needs:

An unlimited number of batches can be created each with its own test parameters and certificates. The operator can select test load and indenter size with party name, address, certificate no. date batch no. and description, high and low limits for readings etc. The previous batches can be reopened for viewing and address change etc.

The B.I.A.S. has built in statistical capabilities with graph and certificates for report generation and printing. It includes frequency distribution and variation graphs.

The system includes calibration and check facilities to calibrate the system and for checking of calibration. This eliminates any system error in measurement.

The range of measurement is form 1mm to 6 mm of diameter with resolution of 0.01 mm.

The Software Includes:

- Facility for Auto / Semi Auto / Manual modes of operation.
- Well managed database saves readings w.r.t. batch and certificate.
- Report generation in the form of certificate and graph as per customer requirements.
- Facility for calibration and check of calibration.

Application:

- To measure Brinell Hardness directly on machine where presently Brinell-Microscope is used. This avoids eye straining of operator on production testing. In addition it gives far better repeated accuracy.
- High-low limits selection enables operator easy acceptance rejection of components.
- Easy to transport anywhere and handy for use with easy setup.

Scope of Supply:


- One hand held unit containing CCD Camera, optics and illumination system with connecting cable.
- USB for Video.
- Brinell Image Analysis System Software.
- PC and windows operating system is to be procured by customer.

Also Available:


- Computerized Brinell Hardness Tester (B 3000 PC)
- Computerized fully automatic Brinell Hardness Tester (B 3000 PC FA)














Result Window



Statistics



Test Certificate



Readings with Impression Window

CANAN TESTING SERVICES

Accredited by NABL (Dept. of Science & Technology-Govt. of India)
11, 1st Floor, Convenient Shopping Centre, Pocket-F, G.T.B Enclave, Nand Nagari, Delhi - 110093

Tel: +91-11-22580160 | +91-11-22583460 | +91-11-2594094

E-mail: canan@canantesting.com Web: www.canantesting.com